

Level Plus®

Magnetostrictive Liquid Level Transmitters
with Tempsonics® Technology

Accessories for liquid level transmitters Catalog



Table of contents

1. Floats 3

1.1 Standard floats 3

1.2 Low-liftoff float 4

1.3 Standard interface floats 5

1.4 Sanitary floats 6

1.5 Teflon® floats 8

1.6 Nitrophyl® floats 9

1.7 Long-gauge floats 9

2. Process meteres and enclosures 11

2.1 Analog process meters 11

2.2 Modbus process meters 12

2.3 Process meter enclosures 12

2.4 Modbus Terminals 12

3. Programming and hardware 13

3.1 Setup software 13

3.2 Hardware 13

4. Magnet and weight assemblies 14

Introduction

MTS Sensors offers a variety of floats to meet your application needs. Our floats come in a variety of sizes from less than 38 mm (1.5 in.) up to 178 mm (7 in.) in diameter. Float materials are available in stainless steel, Teflon®, Aluminum, Hastelloy® C and Nitrophyl®. Product viscosity, specific gravity, and temperature can vary widely in a process or tank gauging application. Because of these variables and others, such as tank pressure and corrosiveness, no one float can meet all requirements. Therefore, a variety of float styles are available and we will assist you in choosing the one that best meets your requirements.

When choosing a float for your application, MTS recommends you choose one that has a specific gravity of at least 0.05 less than that of the measured liquid. For interface measurement, a minimum of 0.05 specific gravity differential is recommended between upper and lower liquids. MTS Sensors also offers a variety of meters, housings, and calibration equipment as accessories to our transmitter range. Meters are available for analog, DDA, and Modbus outputs.




For more information, please contact the MTS Sensors' applications department or go to www.mtssensors.com for more information.

1. Floats

1.1 Standard floats



General notes:

1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. When the magnet is not shown, the magnet is positioned at the center line of float.
4. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.
5. * Standard float that can be expedited

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		29.3 bar (425 psi)	149 °C (300 °F)	No	0.67	Stainless steel	251 981-2*
					0.71	Hastelloy® C	251 981-4
		22.4 bar (325 psi)	149 °C (300 °F)	No	0.48	Stainless steel	251 387-2
		4 bar (60 psi)	149 °C (300 °F)	Yes	0.6	Stainless steel	201 605-2*

Accessories for liquid level transmitters


Catalog

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		69 bar (1000 psi)	149 °C (300 °F)	No	0.65	Stainless steel	254 526-2*
		22.4 bar (325 psi)	149 °C (300 °F)	No	0.45	Stainless steel	251 469-2

1.2 Low-liftoff float

General notes:





1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. When the magnet is not shown, the magnet is positioned at the center line of float.
4. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		8.6 bar (125 psi)	149 °C (300 °F)	Yes	0.65	Stainless steel	252 228-4

1.3 Standard interface floats

General notes:

1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. When the magnet is not shown, the magnet is positioned at the center line of float.
4. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.
5. * Standard float that can be expedited

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		29.3 bar (425 psi)	149 °C (300 °F)	No	0.93	Stainless steel	251 982-2*
						Hastelloy® C	251 982-4
		29.3 bar (425 psi)	149 °C (300 °F)	No	1.06	Stainless steel	251 983-2*
						Hastelloy® C	251 982-4
		4 bar (60 psi)	149 °C (300 °F)	Yes	0.93	Stainless steel	201 606-2*
		69 bar (1000 psi)	149 °C (300 °F)	No	0.93	Stainless steel	254894-2

Controlling design dimensions are in millimeters and measurements in () are in inches


Accessories for liquid level transmitters

Catalog

1.4 Sanitary floats


General notes:

1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. Sanitary polish is available for stainless-steel floats up to 200 Grit/Ra 25.
4. Electropolish is available for stainless-steel floats up to 240 Grit/Ra 15.
5. When the magnet is not shown, the magnet is positioned at the center line of float.
6. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.
7. * Standard float that can be expedited

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		10.3 bar (150 psi)	149 °C (300 °F)	Yes	0.66	Stainless steel 200 Grit / Ra 25 µin (0.625 µm)	401 513-2*
						Stainless steel 240 Grit / Ra 15 µin (0.375 µm)	401 513-4

Note for part no. 401 513-2 & 401 513-4:

- Float meets 3A Sanitary specifications.
- Use this float with all Sanitary transmitter wells as other floats may enter the inactive zone when the tank is emptied.


		22.4 bar (325 psi)	149 °C (300 °F)	Yes	0.63	Stainless steel 200 Grit / Ra 25 µin (0.625 µm)	200 931-6
						Stainless steel 240 Grit / Ra 15 µin (0.375 µm)	200 931-8

Note for part no. 200 931-6 & 200 931-8:

- Float meets 3A Sanitary specifications.
- Float will enter inactive zone when the tank is empty.


General notes:

1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. Sanitary polish is available for stainless-steel floats up to 200 Grit/Ra 25.
4. Electropolish is available for stainless-steel floats up to 240 Grit/Ra 15.
5. When the magnet is not shown, the magnet is positioned at the center line of float.
6. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		8.6 bar (125 psi)	149 °C (300 °F)	Yes	0.48	Stainless steel 240 Grit / Ra 15 µin (0.375 µm)	252 228-2


Note for part no. 252 228-2

Use this float with all Sanitary transmitter wells as other floats may enter the inactive zone when the tank is emptied.

		22.4 bar (325 psi)	149 °C (300 °F)	No	0.74	Stainless steel 200 Grit / Ra 25 µin (0.625 µm)	251 234-2
---	---	-----------------------	--------------------	----	------	--	------------------

Note for part no. 251 234-2:

- Float may enter the inactive zone. Consult factory about viability of usage.

		64 bar (928 psi)	149 °C (300 °F)	Yes	0.86	Stainless steel 240 Grit / Ra 15 µin (0.375 µm)	560 564-2
---	---	---------------------	--------------------	-----	------	--	------------------




Note for part no. 560 564-2

- Float meets 3A Sanitary specifications.
- Float may enter the inactive zone. Consult factory about viability of usage.

1.5 Teflon® floats

General notes:


1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. When the magnet is not shown, the magnet is positioned at the center line of float.
4. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.
5. Floats 251 939, 251 119, and 251 120 should not be used in hazardous areas. Please consult Installation and operation manual for further details.

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		1.7 bar (25 psi)	38 °C (100 °F)	Yes	0.86	Teflon®	201 109-2
					0.93	Teflon®	251 115-2
					1.06	Teflon®	251 116-2
		1.7 bar (25 psi)	38 °C (100 °F)	No	0.86	Teflon®	251 939
		1.7 bar (25 psi)	38 °C (100 °F)	Yes	0.93	Teflon®	251 119
					1.06	Teflon®	251 120

1.6 Nitrophenyl® floats

General notes:



1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. When the magnet is not shown, the magnet is positioned at the center line of float.
4. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.
5. * Standard float that can be expedited

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		17.2 bar (250 psi)	104 °C (220 °F)	Yes	0.45	Nitrophenyl®	201 643-2*
					0.8 – 0.86	Nitrophenyl®	201 649-2
					0.91 – 0.96	Nitrophenyl®	201 650-2



1.7 Long-gauge floats

General notes:

1. Be sure that the float specific gravity is at least 0.05 less than that of the measured liquid as a safety margin at ambient temperature.
2. For interface measurement: A minimum of 0.05 specific gravity differential is required between the upper and lower liquids.
3. When the magnet is not shown, the magnet is positioned at the center line of float.
4. Drawings contained in this document are for reference only. Contact the factory for engineering drawings.
5. * Standard float that can be expedited

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		29.3 bar (425 psi)	149 °C (300 °F)	Yes	0.54	Stainless steel	252 961-2*
					0.65	Hastelloy® C	252 961-4
					0.93	Stainless steel	252 962-2
					0.93	Hastelloy® C	252 962-4
					1.06	Stainless steel	252 963-2
					1.06	Hastelloy® C	252 963-4
		44.8 bar (650 psi)	149 °C (300 °F)	Yes	0.44	Stainless steel	201 248-2
					0.52	Hastelloy® C	201 248-4
					0.93	Stainless steel	252 959-2
					0.93	Hastelloy® C	252 959-4
					1.06	Stainless steel	252 960-2
					1.06	Hastelloy® C	252 960-4

Accessories for liquid level transmitters
Catalog

Photo	Drawing	Pressure	Temperature	Magnet offset	Specific gravity	Material	Part no.
		17.2 bar (250 psi)	149 °C (300 °F)	No	0.44	Stainless steel	251 426-2
					0.47	Hastelloy® C**	251 426-4
					0.93	Stainless steel	251 427-2
					0.93	Hastelloy® C**	251 427-4
					1.06	Stainless steel	251 428-2
		22.4 bar (325 psi)	149 °C (300 °F)	No	0.66	Stainless steel	201 232-2*
					0.70	Hastelloy® C	201 232-4
					0.93	Stainless steel	201 233-2

** Internal diameter for these floats is 34.8 mm (1.37 in.)

2. Process meters and enclosures

2.1 Analog process meters

Photo	Description	Part no.
	LED Display Universal Analog Process Meter (Contact MTS for more options including explosion proof housings.) 6 Digit LED display Input: Analog 4...20 mA Output: None 110 VAC Input Power 32 point linearization Includes 24 Vdc transmitter supply Material: Standard 1/8 in. DIN, high impact plastic, NEMA Type 4X front panel	380 071
	LED Display Universal Analog Process Meter (2 Relays) (Contact MTS for more options including explosion proof housings.) 6 Digit LED display Input: Analog 4...20 mA Output: 2 relays 110 VAC Input Power 32 point linearization Includes 24 Vdc transmitter supply Material: Standard 1/8 in. DIN, high impact plastic, NEMA Type 4X front panel	380 072
	LED Display Universal Analog Process Meter (4 Relays) (Contact MTS for more options including explosion proof housings.) 6 Digit LED display Input: Analog 4-20 mA Output: 4 relays 110 VAC Input Power 32 point linearization Includes 24 Vdc transmitter supply Material: Standard 1/8 in. DIN, high impact plastic, NEMA Type 4X front panel	380 073
	LED Display Universal Analog Process Meter (2 Relays, 4...20 mA) (Contact MTS for more options including explosion proof housings.) 6 Digit LED display Input: Analog 4...20 mA Output: 4...20 mA and 2 relays 110 VAC Input Power 32 point linearization Includes 24 Vdc transmitter supply Material: Standard 1/8 in. DIN, high impact plastic, NEMA Type 4X front panel	380 095
	XP Loop Powered Analog Meter Loop Powered on 4...20 mA output Displays in Percentage Only Embedded in XP Housing XP: Class I, II, III; Division 1; Groups B-G IS: Class I, II, III; Division 1; Groups A-G	380 062
	Loop Powered Analog Meter Loop Powered on 4...20 mA output Displays loop current, engineering units, and/or value Selectable on screen engineering units IP 67 / NEMA Type 4X Intrinsically Safe, backlight	380 088

2.2 Modbus process meters

Photo	Description	Part no.
	Multivariable Modbus Process Meter Display levels in feet, inches, and 16ths of an inch Input: RS485 Modbus RTU Output: 2 Form A relays and 4...20 mA 110 VAC Input Power 16 point linearization Includes 24 Vdc transmitter supply Material: Standard 1/8 in. DIN, high impact plastic, NEMA Type 4X front panel	380 086
	Single Variable Modbus Process Meter (Contact MTS for more options including explosion proof housings.) 6 Digit Display in Decimal Format Display 1 process variable without interrupting Master/Slave communication Input: RS485 Modbus RTU Output: 2 Form A relays and 4...20 mA 110 VAC Input Power 16 point linearization Includes 24 Vdc transmitter supply Material: Standard 1/8 in. DIN, high impact plastic, NEMA Type 4X front panel	380 094

2.3 Process meter enclosures

Photo	Description	Part no.
	NEMA Enclosures - Single NEMA 4X <i>(NEMA Enclosures are available for most process meters, please contact factory for more information.)</i>	401 150
	NEMA Enclosures - Dual NEMA 4X <i>(NEMA Enclosures are available for most process meters, please contact factory for more information.)</i>	401 151

2.4 Modbus Terminals

Photo	Description	Part no.
	LCD Modbus Terminal Displays up to 4 tanks (2 levels, temp, volume) Displays up to 8 tanks (2 levels, temp) Displays levels in ft., in, and 16ths in. Input: Up to 8 Modbus transmitters Output: Modbus Mounted in NEMA 4 box Class 1 Div. 2 Includes Power Supply Calibrate from Screen	280 494-X
	Touchscreen Modbus Terminal Displays up to 16 tanks (2 levels, temp, volume) Displays levels in ft., in, and 16ths in. Input: up to 16 Modbus transmitters Output: Modbus Pictorial display of tanks Touchscreen Mounted in NEMA 4 box Class 1 Div. 2 Includes Power Supply Calibrate from Screen	280 508-X

3. Programming and hardware





3.1 Setup software

Photo	Description	Part no.
	LP-Dashboard on USB	551 719

3.2 Hardware

Photo	Description	Part no.
	HART to USB adapter	380 068
	RS-485 to USB adapter converter	380 114
	Hex Bushing 2 in. MNPT × 3/4 in. FNPT	561 440
	Hex Bushing 2 in. FNPT × 4 in. MNPT	561 441
	Hex Bushing 1 in. FNPT × 2 in. MNPT	561 448

4. Magnet and weight assemblies

Photo	Drawing	Description	Part no.
		150 lb. Pull Magnet For Tank SLAYER® level transmitter. (Washer must be removed before installation)	560 604
		Standard 11 lb. Weight For LP-Series transmitters	401 059
		Low Lutoff 11 lb. Weight Assembly	402 364
		Narrow 11 lb. Weight Use with LP-Series transmitters	402 647

UNITED STATES 3001 Sheldon Drive
MTS Systems Corporation Cary, N.C. 27513
Sensors Division Phone: +1 919 677-0100
E-mail: info.us@mtssensors.com

GERMANY Auf dem Schüffel 9
MTS Sensor Technologie 58513 Lüdenscheid
GmbH & Co. KG Phone: +49 2351 9587-0
E-mail: info.de@mtssensors.com

ITALY Phone: +39 030 988 3819
Branch Office E-mail: info.it@mtssensors.com

FRANCE Phone: +33 1 58 4390-28
Branch Office E-mail: info.fr@mtssensors.com

GREAT BRITAIN Phone: +44 79 44 15 03 00
Branch Office E-mail: info.uk@mtssensors.com

CHINA Phone: +86 21 6485 5800
Branch Office E-mail: info.cn@mtssensors.com

JAPAN Phone: +81 3 6416 1063
Branch Office E-mail: info.jp@mtssensors.com

Document Part Number:

551103 Revision H (EN) 08/2018



www.mtssensors.com

MTS, Temposonics and Level Plus are registered trademarks of MTS Systems Corporation in the United States; MTS SENSORS and the MTS SENSORS logo are trademarks of MTS Systems Corporation within the United States. These trademarks may be protected in other countries. All other trademarks are the property of their respective owners. Copyright © 2018 MTS Systems Corporation. No license of any intellectual property rights is granted. MTS reserves the right to change the information within this document, change product designs, or withdraw products from availability for purchase without notice. Typographic and graphics errors or omissions are unintentional and subject to correction. Visit www.mtssensors.com for the latest product information.